

Sampler Tubus



Sampler for pourable bulk goods up to approx. 1 cm in diameter. This makes it possible, for example, to remove hazel nuts, blends of tea, grain or similar items from large sacks.

- ▶ Also for coarse-grained bulk goods
- ▶ Made of stainless steel AISI 316L (1.4404)
- ▶ Special geometry of the tip

i Corresponds to ISTA standard for seed lengths of 10 mm (wheat, oats) and 5 mm (flax, vetches).

Use

1. Insert Tubus into a sack to the desired sampling depth, while keeping the collection tube closed using your hand.
2. When you remove your hand, the sample flows directly through the open tube into the container or sampling bag beneath it.

| Sampler Tubus | | |
|-------------------------------|----------|--------------|
| Length cm | Dia. mm | Item no. |
| 40 | 40 | 5382-0040 N4 |
| 80 | 40 | 5382-0080 N4 |
| Accessories | | |
| Description | Item no. | |
| Control seal close-it page 78 | | |

QuickPicker



The core sampler QuickPicker is particularly suitable in the event that bulk goods are taken directly from sacks or bags and have to be filled into the original sampling bottle directly.

QuickPicker is uncomplicated in its use and cleaning. No undercuts or edges mean no sample residues which could falsify subsequent samples. It is therefore ideal for quality control.

The sampler QuickPicker is delivered complete with two 250 ml PE sample bottles and with a cleaning brush.

QuickPicker | collects samples quickly and channels them directly into the sampling bottle



- ▶ Insertion depth 30 cm, diameter 25 mm
- ▶ Made of stainless steel AISI 316L (1.4404) or PP transparent for aggressive chemicals, scratchproof, sterilisable, cost-effective
- ▶ Removable tip, easy cleaning
- ▶ Additional sampling bottles made of PE or PP available as accessories



i Corresponds to ISTA standard for seed lengths of 10 mm (wheat, oats) and 5 mm (flax, vetches).



close-it seals and close-it food & pharma lock seals ensure non-leak closure of the insertion point in bags and BigBags. See page 78.

QuickPicker AISI 316L in use

QuickPicker

| Material | Insertion depth mm | Total length cm | Volume ml | Item no. |
|-----------------|--------------------|-----------------|-----------|--------------|
| AISI 316L | 300 | 50 | 75 | 5322-1300 N4 |
| PP, transparent | 300 | 50 | 75 | 5322-0300 N4 |

Accessories

| Description | Item no. |
|--------------------------------|--------------|
| Sampling bottle LDPE, 250 ml | 0318-0250 N3 |
| Sampling bottle PP, 250 ml | 0319-0250 N3 |
| Transport case for QuickPicker | 3600-3000 N3 |
| close-it seals page 78 | |